

Conversion Table Temperature Sensors Food: TFP - TSB (Big Head)



Old TFP	TSB - Big Head	TSBF process connection	Spacer	Transmitter	Electrical connections	Comments
TFP-40	TSBF-Big head	G01- G1/2" Thread connections	corresponding TFP had no spacer (for TSBF spacer optional available)	0 or 1	PG or M12	
TFP-40-G1/4"	TSBF-Big head	G02-G1/4" Thread connections	corresponding TFP had no spacer (for TSBF spacer optional available)	0 or 1	PG or M12	
TFP-41	TSBF-Big head	C02-G1/2" Hygiene connections	corresponding TFP had no spacer (for TSBF spacer optional available)	0 or 1	PG or M12	
TFP-42	TSBF-Big head	C01-M12 Hygiene connections	corresponding TFP had no spacer (for TSBF spacer optional available)	0 or 1	PG or M12	
TFP-43	TSBF-Big head	C04 -Front flush connections(with 3A, not fully front flush with 1 mm ingressiion) or C06-Front flush connections (without 3A, real front flush without 1 mm ingressiion)	corresponding TFP had no spacer (for TSBF spacer optional available)	0 or 1	PG or M12	
TFP-44	TSBF-Big head	C03 -Front flush connections (with 3A, not fully front flush with 1 mm ingressiion) or C05-Front flush connections (without 3A, real front flush without 1 mm ingressiion)	corresponding TFP had no spacer (for TSBF spacer optional available)	0 or 1	PG or M12	
TFP-47...C25	TSBF-Big head	T05-Triclamp connection	corresponding TFP had no spacer (for TSBF spacer optional available)	0 or 1	PG or M12	
TFP-47...C34	TSBF-Big head	T10-Triclamp connection	corresponding TFP had no spacer (for TSBF spacer optional available)	0 or 1	PG or M12	
TFP-47...C50	TSBF-Big head	TC1-Triclamp connection	corresponding TFP had no spacer (for TSBF spacer optional available)	0 or 1	PG or M12	
TFP-47...C64	TSBF-Big head	TC2-Triclamp connection	corresponding TFP had no spacer (for TSBF spacer optional available)	0 or 1	PG or M12	
TFP-47...C77	TSBF-Big head	T25-Triclamp connection	corresponding TFP had no spacer (for TSBF spacer optional available)	0 or 1	PG or M12	
TFP-47...C91	TSBF-Big head	TC3-Triclamp connection	corresponding TFP had no spacer (for TSBF spacer optional available)	0 or 1	PG or M12	
TFP-49	TSBF-Big head	N01-Plain rod without thread	corresponding TFP had no spacer (for TSBF spacer optional available)	0 or 1	PG or M12	
TFP-50	TSBF-Big head	G01- G1/2" Thread connections	TFP had spacer, for TSBF select spacer S or H	0 or 1	PG or M12	
TFP-50-G1/4"	TSBF-Big head	G02-G1/4" Thread connections	TFP had spacer, for TSBF select spacer S or H	0 or 1	PG or M12	
TFP-51	TSBF-Big head	C02-G1/2" Hygiene connections	TFP had spacer, for TSBF select spacer S or H	0 or 1	PG or M12	
TFP-52	TSBF-Big head	C01-M12 Hygiene connections	TFP had spacer, for TSBF select spacer S or H	0 or 1	PG or M12	
TFP-54	TSBF-Big head	C03 -Front flush connections (with 3A, not fully front flush with 1 mm ingressiion) or C05-Front flush connections (without 3A, real front flush without 1 mm ingressiion)	TFP had spacer, for TSBF select spacer S or H	0 or 1	PG or M12	
TFP-57...C25	TSBF-Big head	T05-Triclamp connection	TFP had spacer, for TSBF select spacer S or H	0 or 1	PG or M12	
TFP-57...C34	TSBF-Big head	T10-Triclamp connection	TFP had spacer, for TSBF select spacer S or H	0 or 1	PG or M12	
TFP-57...C50	TSBF-Big head	TC1-Triclamp connection	TFP had spacer, for TSBF select spacer S or H	0 or 1	PG or M12	
TFP-57...C64	TSBF-Big head	TC2-Triclamp connection	TFP had spacer, for TSBF select spacer S or H	0 or 1	PG or M12	
TFP-57...C77	TSBF-Big head	T25-Triclamp connection	TFP had spacer, for TSBF select spacer S or H	0 or 1	PG or M12	
TFP-57...C91	TSBF-Big head	TC3-Triclamp connection	TFP had spacer, for TSBF select spacer S or H	0 or 1	PG or M12	
TFP-59	TSBF-Big head	M02 FlexAdapt G3/8" connection	corresponding TFP had no spacer (TSBF optional spacer available)	0 or 1	PG or M12	incl. with cap nut sensor tip 3 mm, with standard probe length of 37, 59,83,97,160 mm
TFP-60	TSBF-Big head	G01- G1/2" Thread connections	corresponding TFP had no spacer (for TSBF spacer optional available)	2	2 x M12	
TFP-61	TSBF-Big head	C02-G1/2" Hygiene connections	corresponding TFP had no spacer (for TSBF spacer optional available)	2	2 x M12	
TFP-62	TSBF-Big head	C01-M12 Hygiene connections	corresponding TFP had no spacer (for TSBF spacer optional available)	2	2 x M12	
TFP-67...C25	TSBF-Big head	T05-Triclamp connection	corresponding TFP had no spacer (for TSBF spacer optional available)	2	2 x M12	
TFP-67...C34	TSBF-Big head	T10-Triclamp connection	corresponding TFP had no spacer (for TSBF spacer optional available)	2	2 x M12	
TFP-67...C50	TSBF-Big head	TC1-Triclamp connection	corresponding TFP had no spacer (for TSBF spacer optional available)	2	2 x M12	
TFP-67...C64	TSBF-Big head	TC2-Triclamp connection	corresponding TFP had no spacer (for TSBF spacer optional available)	2	2 x M12	
TFP-67...C77	TSBF-Big head	T25-Triclamp connection	corresponding TFP had no spacer (for TSBF spacer optional available)	2	2 x M12	
TFP-67...C91	TSBF-Big head	TC3-Triclamp connection	corresponding TFP had no spacer (for TSBF spacer optional available)	2	2 x M12	
TFP-68	TSBF-Big head	M02 FlexAdapt G3/8" connection	corresponding TFP had no spacer (for TSBF spacer optional available)	2	2 x M12	incl. with cap nut sensor tip 3 mm, with standard probe length of 37, 59,83,97,160 mm
TFP-69	TSBF-Big head	N01-Plain rod without thread	corresponding TFP had no spacer (for TSBF spacer optional available)	2	2 x M12	
TFP-113	TSBF-Big head	C04 -Front flush connections(with 3A, not fully front flush with 1 mm ingressiion) or C06-Front flush connections (without 3A, real front flush without 1 mm ingressiion)	corresponding TFP had no spacer (for TSBF spacer optional available)	0 or 1	PG or M12	
TFP-414	TSBF-Big head	G03-G1/4" Thread connections	corresponding TFP had no spacer (for TSBF spacer optional available)	0 or 1	PG or M12	incl. with spring loaded cap nut sensor tip 3mm, with standard probe length of 36,61,75,93,100,105,115,120,130,140,160 mm

Conversion Table Temperature Sensors Food: TFP - TSM (Mini Head)



HYGIENIC BY DESIGN

ANDERSON-NEGELE

Old TFP	TSM - Mini Head	TSMF Process connections	Spacer	Transmitter	Electrical Connection	Comments
TFP-159	TSMF -Mini head	M03-G3/8" Thread connections	corresponding TFP had no spacer (for TSMF spacer optional available)	0 or 1	only M12	incl. with cap nut sensor tip 4 mm, with standard probe length of 68,148,198,234,238,249 mm
TFP-160	TSMF -Mini head	G01- G1/2" Thread connections	corresponding TFP had no spacer (for TSMF spacer optional available)	0 or 1	only M12	
TFP-160-G1/4"	TSMF -Mini head	G02-G1/4" Thread connections	corresponding TFP had no spacer (for TSMF spacer optional available)	0 or 1	only M12	
TFP-160-G3/8"	TSMF -Mini head	M04-G3/8" Thread connections	corresponding TFP had no spacer (for TSMF spacer optional available)	0 or 1	only M12	incl. with spring loaded cap nut sensor tip 4 mm, with standard probe length of 68,148,198,234,238,249 mm
TFP-161	TSMF -Mini head	C02-G1/2" Hygiene connections	corresponding TFP had no spacer (for TSMF spacer optional available)	0 or 1	only M12	
TFP-162	TSMF -Mini head	C01-M12 Hygiene connections	corresponding TFP had no spacer (for TSMF spacer optional available)	0 or 1	only M12	
TFP-163	TSMF -Mini head	C04 -Front flush connections(with 3A, not fully front flush with 1 mm ingress) or C06-Front flush connections (without 3A, real front flush without 1 mm ingress)	corresponding TFP had no spacer (for TSMF spacer optional available)	0 or 1	only M12	
TFP-164	TSMF -Mini head	C03 -Front flush connections (with 3A, not fully front flush with 1 mm ingress) or C05-Front flush connections (without 3A, real front flush without 1 mm ingress)	corresponding TFP had no spacer (for TSMF spacer optional available)	0 or 1	only M12	
TFP-167...C25	TSMF -Mini head	T05-Triclap connection	corresponding TFP had no spacer (for TSMF spacer optional available)	0 or 1	only M12	
TFP-167...C34	TSMF -Mini head	T10-Triclap connection	corresponding TFP had no spacer (for TSMF spacer optional available)	0 or 1	only M12	
TFP-167...C50	TSMF -Mini head	TC1-Triclap connection	corresponding TFP had no spacer (for TSMF spacer optional available)	0 or 1	only M12	
TFP-167...C64	TSMF -Mini head	TC2-Triclap connection	corresponding TFP had no spacer (for TSMF spacer optional available)	0 or 1	only M12	
TFP-167...C77	TSMF -Mini head	T25-Triclap connection	corresponding TFP had no spacer (for TSMF spacer optional available)	0 or 1	only M12	
TFP-167...C91	TSMF -Mini head	TC3-Triclap connection	corresponding TFP had no spacer (for TSMF spacer optional available)	0 or 1	only M12	
TFP-169	TSMF -Mini head	N01-Plain rod without thread	corresponding TFP had no spacer (for TSMF spacer optional available)	0 or 1	only M12	
TFP-179	TSMF -Mini head	M02 FlexAdapt G3/8" connection	corresponding TFP had no spacer (for TSMF spacer optional available)	0 or 1	only M12	incl. with cap nut sensor tip 3mm, with standard probe length of 37, 59,83,97,160 mm
TFP-180	TSMF -Mini head	G01- G1/2" Thread connections	corresponding TFP had no spacer (for TSMF spacer optional available)	0 or 1	Fixed Cable	
TFP-180-G1/4"	TSMF -Mini head	G02-G1/4" Thread connections	corresponding TFP had no spacer (for TSMF spacer optional available)	0 or 1	Fixed Cable	
TFP-181	TSMF -Mini head	M04-G3/8" Thread connections	corresponding TFP had no spacer (for TSMF spacer optional available)	0 or 1	Fixed Cable	incl. with spring loaded cap nut sensor tip 4 mm, with standard probe length of 68,148,198,234,238,249 mm
TFP-182	TSMF -Mini head	C02-G1/2" Hygiene connections	corresponding TFP had no spacer (for TSMF spacer optional available)	0 or 1	Fixed Cable	
TFP-183	TSMF -Mini head	C01-M12 Hygiene connections	corresponding TFP had no spacer (for TSMF spacer optional available)	0 or 1	Fixed Cable	
TFP-184	TSMF -Mini head	C04 -Front flush connections(with 3A, not fully front flush with 1 mm ingress) or C06-Front flush connections (without 3A, real front flush without 1 mm ingress)	corresponding TFP had no spacer (for TSMF spacer optional available)	0 or 1	Fixed Cable	
TFP-189	TSMF -Mini head	C03 -Front flush connections (with 3A, not fully front flush with 1 mm ingress) or C05-Front flush connections (without 3A, real front flush without 1 mm ingress)	corresponding TFP had no spacer (for TSMF spacer optional available)	0 or 1	Fixed Cable	
TFP-199	TSMF -Mini head	M02 FlexAdapt G3/8" connection	corresponding TFP had no spacer (for TSMF spacer optional available)	0 or 1	Fixed Cable	included with cap nut sensor tip 3 mm, with standard probe length of 37, 59,83,97,160 mm
TFP-614	TSMF -Mini head	G03-G1/4" Thread connections	corresponding TFP had no spacer (for TSMF spacer optional available)	0 or 1	only M12	included with spring loaded cap nut with sensor tip 3 mm, with standard probe length of 36,61,75,93,100,105,115,120,130,140,160 mm
TFP-814	TSMF -Mini head	G03-G1/4" Thread connections	corresponding TFP had no spacer (for TSMF spacer optional available)	0 or 1	Fixed Cable	included with spring loaded cap nut with sensor tip 3 mm, with standard probe length of 36,61,75,93,100,105,115,120,130,140,160 mm