

Conversion Table Temperature Sensors Food: TFP - TSM (Mini Head)



Old TFP	TSM - Mini Head	TSMF Process connections	Spacer	Transmitter	Electrical Connection	Comments
TFP-159	TSMF -Mini head	M03-G3/8" Thread connections	corresponding TFP had no spacer (for TSMF spacer optional available)	0 or 1	only M12	incl. with cap nut sensor tip 4 mm, with standard probe length of 68,148,198,234,238,249 mm
TFP-160	TSMF -Mini head	G01- G1/2" Thread connections	corresponding TFP had no spacer (for TSMF spacer optional available)	0 or 1	only M12	
TFP-160-G1/4"	TSMF -Mini head	G02-G1/4" Thread connections	corresponding TFP had no spacer (for TSMF spacer optional available)	0 or 1	only M12	
TFP-160-G3/8"	TSMF -Mini head	M04-G3/8" Thread connections	corresponding TFP had no spacer (for TSMF spacer optional available)	0 or 1	only M12	incl. with spring loaded cap nut sensor tip 4 mm, with standard probe length of 68,148,198,234,238,249 mm
TFP-161	TSMF -Mini head	C02-G1/2" Hygiene connections	corresponding TFP had no spacer (for TSMF spacer optional available)	0 or 1	only M12	
TFP-162	TSMF -Mini head	C01-M12 Hygiene connections	corresponding TFP had no spacer (for TSMF spacer optional available)	0 or 1	only M12	
TFP-163	TSMF -Mini head	C04 -Front flush connections(with 3A, not fully front flush with 1 mm ingress) or C06-Front flush connections (without 3A, real front flush without 1 mm ingress)	corresponding TFP had no spacer (for TSMF spacer optional available)	0 or 1	only M12	
TFP-164	TSMF -Mini head	C03 -Front flush connections (with 3A, not fully front flush with 1 mm ingress) or C05-Front flush connections (without 3A, real front flush without 1 mm ingress)	corresponding TFP had no spacer (for TSMF spacer optional available)	0 or 1	only M12	
TFP-167...C25	TSMF -Mini head	T05-Triclamp connection	corresponding TFP had no spacer (for TSMF spacer optional available)	0 or 1	only M12	
TFP-167...C34	TSMF -Mini head	T10-Triclamp connection	corresponding TFP had no spacer (for TSMF spacer optional available)	0 or 1	only M12	
TFP-167...C50	TSMF -Mini head	TC1-Triclamp connection	corresponding TFP had no spacer (for TSMF spacer optional available)	0 or 1	only M12	
TFP-167...C64	TSMF -Mini head	TC2-Triclamp connection	corresponding TFP had no spacer (for TSMF spacer optional available)	0 or 1	only M12	
TFP-167...C77	TSMF -Mini head	T25-Triclamp connection	corresponding TFP had no spacer (for TSMF spacer optional available)	0 or 1	only M12	
TFP-167...C91	TSMF -Mini head	TC3-Triclamp connection	corresponding TFP had no spacer (for TSMF spacer optional available)	0 or 1	only M12	
TFP-169	TSMF -Mini head	N01-Plain rod without thread	corresponding TFP had no spacer (for TSMF spacer optional available)	0 or 1	only M12	
TFP-179	TSMF -Mini head	M02 FlexAdapt G3/8" connection	corresponding TFP had no spacer (for TSMF spacer optional available)	0 or 1	only M12	incl. with cap nut sensor tip 3mm, with standard probe length of 37, 59,83,97,160 mm
TFP-180	TSMF -Mini head	G01- G1/2" Thread connections	corresponding TFP had no spacer (for TSMF spacer optional available)	0 or 1	Fixed Cable	
TFP-180-G1/4"	TSMF -Mini head	G02-G1/4" Thread connections	corresponding TFP had no spacer (for TSMF spacer optional available)	0 or 1	Fixed Cable	
TFP-181	TSMF -Mini head	M04-G3/8" Thread connections	corresponding TFP had no spacer (for TSMF spacer optional available)	0 or 1	Fixed Cable	incl. with spring loaded cap nut sensor tip 4 mm, with standard probe length of 68,148,198,234,238,249 mm
TFP-182	TSMF -Mini head	C02-G1/2" Hygiene connections	corresponding TFP had no spacer (for TSMF spacer optional available)	0 or 1	Fixed Cable	
TFP-183	TSMF -Mini head	C01-M12 Hygiene connections	corresponding TFP had no spacer (for TSMF spacer optional available)	0 or 1	Fixed Cable	
TFP-184	TSMF -Mini head	C04 -Front flush connections(with 3A, not fully front flush with 1 mm ingress) or C06-Front flush connections (without 3A, real front flush without 1 mm ingress)	corresponding TFP had no spacer (for TSMF spacer optional available)	0 or 1	Fixed Cable	
TFP-189	TSMF -Mini head	C03 -Front flush connections (with 3A, not fully front flush with 1 mm ingress) or C05-Front flush connections (without 3A, real front flush without 1 mm ingress)	corresponding TFP had no spacer (for TSMF spacer optional available)	0 or 1	Fixed Cable	
TFP-199	TSMF -Mini head	M02 FlexAdapt G3/8" connection	corresponding TFP had no spacer (for TSMF spacer optional available)	0 or 1	Fixed Cable	included with cap nut sensor tip 3 mm, with standard probe length of 37, 59,83,97,160 mm
TFP-614	TSMF -Mini head	G03-G1/4" Thread connections	corresponding TFP had no spacer (for TSMF spacer optional available)	0 or 1	only M12	included with spring loaded cap nut with sensor tip 3 mm, with standard probe length of 36,61,75,93,100,105,115,120,130,140,160 mm
TFP-814	TSMF -Mini head	G03-G1/4" Thread connections	corresponding TFP had no spacer (for TSMF spacer optional available)	0 or 1	Fixed Cable	included with spring loaded cap nut with sensor tip 3 mm, with standard probe length of 36,61,75,93,100,105,115,120,130,140,160 mm